# Ki Spark







### FORM ADDS FUNCTION

The unique contour of the Spark's backrest increases the usable depth of the seating system by allowing the seat to move underneath the back by an extra 2". This innovative design also comes with 32° of built-in angle-adjustability and the ability to change the depth by 4", in 1" increments



#### SIMPLICITY IS CATCHING

With a clean, ergonomic, easy-to-release latch, the chair folds into an incredibly small package and opens again with a snap! Spark uses an aesthetically pleasing frame extender keeping the length of the frame shorter and stronger and making the chair more manageable for the user and caretaker.



#### **DIRECT MOUNT HANGERS**

Our new 70°, 80° and 90° hangers have been redesigned to allow for very short leg lengths. With a minimum footrest length of 3 ¾" and adjustments in ½" increments, the best hanger in the industry now works great for kids!

#### EASIER ON THE EYE

The Spark uses an aesthetically pleasing frame extender to keep the length of the frame shorter and stronger while allowing for up to 4" of depth adjustability when you need it. This keeps the frame manageable for the rider and the caretaker.

#### **UP-IN-ARMS**

The Flip-Up arm is angle, height, and length adjustable giving unmatched flexibility when setting up a seating system.

#### FRONT FRAME STYLES

Spark offers the option of a swing away front end featuring our patented footrests or 70 $^{\circ}$  or 80 $^{\circ}$  fixed frames. The swing away hangers come in 4 bends (60, 70, 80 & 90) are light and easy to use and so strong we offer a lifetime warranty.

#### TRANSIT APPROVED

Transit tested and approved for added safety and securement during transport.



## **SPECIFICATIONS**

Transport Weight:	17.5 lbs.*	7.94 kg*
Seat Width:	10-16 in.	25-41 cm
Seat Depth:	12-18 in.	31-46 cm
Front Seat Height:	13-21 in.	33-53 cm
Rear Seat Height:	11-18.5 in.	28-47 cm
Top Tubing Size:	1 in.	2.54 cm
Bottom Tubing Size:	1 in.	2.54 cm
Weight Capacity:	168 lbs.	76 kg
Ansi Resna WC-19 Transit:	Yes	Yes

12"x12" Frame with Stroller Handle Back Posts, and 5" Poly Casters. Armrests, Footrest and Rear Wheels removed.

## A UNIQUE PEDIATRIC WHEELCHAIR

Spark is designed to be used with virtually any clinically prescribed seating system.



